

ONE TOUCH FITTINGS

Series WP2

Cat No WP2 - 01 - D

Tube



Tube OD in mm		Ø4	Ø6	Ø8	Ø10	Ø12
Ordering no. for	Nylon	WH01W04	WH01W06	WH01W08	WH01W10	WH01W12
	PU	WH00B04	WH00B06	WH00B08	WH00B10	WH00B12

Colour: Nylon - White PU - Blue

Usage instructions

(For maximum efficiency)


- Cut the tube - end burr free and square, using **Tube cutter (WC1)** and clean the edge to ensure leak tight joints. (Do not use blunt tools / hacksaw / chisel etc.,)
- Ensure the tube is fully inserted into the fitting - until the positive stop, beyond the '**U**' seal.
- Tightening torque for threaded components

Thread size	Tightening torque Nm
M5	1 - 1.5
1/8	7 - 9
1/4	12 - 14
3/8	22 - 24
1/2	28 - 30

- Minimum bend radius of the tubing to avoid leakage

Min. bend radius for (in mm)	OD of tube	Ø4	Ø6	Ø8	Ø10	Ø12
	Nylon	15	30	50	65	90
	PU	10	15	25	30	35

Tube Cutter



Ordering No	WC1
-------------	-----

Can cut tubes upto Ø12mm OD

How to Order

While ordering fittings, mention the Ordering number given in the corresponding tables, and for tubes, mention the ordering number with required length in metres.

Subject to change